







Cross-section detail
Scale 5:1



*wire 1mm² - part of power cable L=200mm

Notes :
Power: 1100W +5%/ -10%
Voltage: 230V
Temperature: 40/50°C
Resistance: 48,09 Ohm; 2,1 Ohm/m
Silicone heating wire length: 22,9m
Alufoil on both side




REV.	DATE	DESCRIPTION	PREPARED	CHECKED	APPROVED
1	18/02/2026	-	US	DR	BKG
0	06/12/2025	-	US	DR	BKG

HGI NUMBER:	CUSTOMER NUMBER:	DRAWING NUMBER
410098603010P	RK40773	PCA-REK-041

VENDOR:	CONTRACT NO. :	VENDOR JOB NO.:
REKUBIK	---	X-XXXX-XXXX

SCALE	SIZE	DOCUMENT NO.:	SHEET	REV
NTS	A3	X-XXXX-XXXX	01 OF 04	00



1	18/02/2026	-	US	DR	BKG
0	06/12/2025	-	US	DR	BKG
REV.	DATE	DESCRIPTION	PREPARED	CHECKED	APPROVED
HGI NUMBER:			CUSTOMER NUMBER:		DRAWING NUMBER
410098603010P			RK40773		PCA-REK-041
CONTRACT NO. : --			VENDOR JOB NO.: X-XXXX-XXXX		
SCALE	SIZE	DOCUMENT NO.: X-XXXX-XXXX			REV
NTS	A3				00
				SHEET 02 OF 04	



REKUBIK : HANG MANS PCL-086-49

POS.	PART NUMBER	QTY.	DESCRIPTION
1	ALUFOIL-HT-50	2	Aluminum foil adhesive 50±10 micron, service temperature 120°C (730mmx1100mm)
2	C1S-2.1-3-T1	1	Silicone heating cable 2.1 ohm/m without braiding (L=22.9 m)
3	CB-1000x15	18	Cardboard grey, spacer 1850gsm (1000mmx15mm)
4	CB-730x1100	1	Cardboard grey with cutout 350gsm (730mmx1100mm)
5	SS 6-2 BL	4	Shrink sleeve with glue 6/2 black (L=0.035m)
6	IN-0.5-1.5-01	4	In-line connector 0.5-1.5mm ² Cu tinned uninsulated
7	LRB-1,0T-M4	1	Ring tongue terminal 0.5-1mm ² M4 tinned brass uninsulated double crimp (LRB)
8	STK-HOT	1	Sticker "Hot surface" Yellow, platified, Attention Hot
9	PC-EURO-PLUG-3x1.00	1	Power cable EURO 3x1mm ² -3m black 10A/250V
10	LB-PC-PCA-REK-04	1	Label for power cable_vinyl_green
11	STK-02	1	Label paper 105x37 mm A4 white matte
12	HT31 - 10A40	1	Thermostat (open +40±3°C, reset +29±4°C)
13	HT31 - 10A50	1	Thermostat (open +50±3°C, reset +39±4°C)
14	M4-DIN522-01	1	Repair washer 4x20x1.2 DIN522 steel zinc plated
15	RV-4X5-01	1	Flat head blind revit 4x5
16	HSS 10-120	1	Heat shrink sleeve with glue ID 10mm black (L=0.12m)
17	HT31 - 10A15	2	Thermostat (open +15±5°C, reset +5±5°C)

1	18/02/2026	-	US	DR	BKG
0	06/12/2025	-	US	DR	BKG
REV.	DATE	DESCRIPTION	PREPARED	CHECKED	APPROVED
HGI NUMBER:		CUSTOMER NUMBER:		DRAWING NUMBER	
410098603010P		RK40773		PCA-REK-041	
CONTRACT NO. : --			VENDOR JOB NO.: X-XXXX-XXXX		
SCALE	SIZE	DOCUMENT NO.: X-XXXX-XXXX		SHEET 03 OF 04	REV 00
NTS	A3				



FILENAME : HEATING MATS PCA-REK-041


STK-02

**REKUBIK®** 

Ref: PCA-REK_041
Rating: 230Vac, 1100W;
Date: DD/MM/YYYY
Quality check:

40/50°C

STK-HOT



LB-PC-SI-XXX_XX

Gebrauchsanweisung:
Gegenstand: PCA-REK_041

— Anwendungsbereich: Heizung von IBC-Container

- Die Verwendung der PCA-Matte ist nur für einen IBC-Container erlaubt.
- Die Verwendung dieser PCA-Matte erfordert die Verwendung der sichtbaren "HOT"-Wärme Etiketten auf der Außenseite des Containers.
- Die Heizmatte sollte für den IBC-Behälter verwendet werden, der mit dem zu beheizenden Produkt von unten gefüllt ist. Während der IBC-Behälter und das Produkt der maximalen Temperatur standhalten sollten. Des Heizdrahtes, eingestellt durch die Temperaturbegrenzer auf der Heizmatte.

— Folgende Bedingungen sind zu beachten:

- o Die Heizmatte kann für 230V verwendet werden.
- o Die Verwendung des entsprechenden Spannungsadapterkabels ist zwingend erforderlich.
- o Die Stromversorgung ist mit einem Fehlerstromschutzschalter von 30mA und 16A Schutzschalter zu sichern.
- o Die Heizmatte ist für den einmaligen Gebrauch ausgelegt.
- o Die Heizmatte sollte vor dem Abgeben ausgeschaltet werden.
- o IBC-Behälter mit Heizmatte sollte in trockener Atmosphäre gelagert und verwendet werden
Mit Umgebungstemperatur zwischen + 10 ° und + 25 ° C (50 ° - 77 ° F).
- o Ziehen Sie nicht am Kabel.

• In den folgenden Fällen darf die Heizmatte nicht verwendet werden:

- o Die Heizmatte darf nicht im Falle eines leeren oder geneigten IBC-Behälters verwendet werden.
- o Die Heizmatte ist nicht für den Einsatz mit einem BIB "Beutel in einer Schachtel" ausgelegt.
- o Die Heizmatte darf nicht in EX-Zonen verwendet werden.
- o Verwenden Sie die Heizmatte niemals in Verbindung mit einem Heizraum.
- o Der IBC-Behälter kann während des Heizvorgangs nicht durch einen Isoliermantel abgedeckt werden.

Aluminium-Heizmatte für IBC

- 230Vac, 1100W
- PCA-REK_041
- Thermostat: 40/50°C

230V



**REKUBIK®**

1	18/02/2026	—	US	DR	BKG
0	06/12/2025	—	US	DR	BKG
REV.	DATE	DESCRIPTION	PREPARED	CHECKED	APPROVED
HGI NUMBER: 410098603010P					
CUSTOMER NUMBER: RK40773			DRAWING NUMBER: PCA-REK-041		
CONTRACT NO. : --			VENDOR JOB NO.: X-XXXX-XXXX		
SCALE	SIZE	DOCUMENT NO.: X-XXXX-XXXX		SHEET 04 OF 04	REV 00
NTS	A3				

VENDOR:

**REKUBIK®**